

SPIRAL DESIGN ANODIZED ALUMINUM GRAINSPEAR SAMPLER



Highly representative sampling is fast and simple with our aluminium grain Spear sampler. This spiral sampler is easy to use and gives great results.

The spiral position of the pockets gives superior sampling results. This means the bottom pocket opens and fills first giving a more representative sample.

The sampler is particularly suited for larger powders, granule and grain sampling. This can be from IBC, kegs, silos, railway trucks, ships and almost all applications

The lightweight aluminium construction means even the long samplers are easy to operate and handle. The tip is fixed permanently so it can not be lost.

(Pictured with Heavy Duty Handle for Grain Spear 2500 mm)



The lightweight aluminium construction means even the long samplers are easy to operate and handle. The tip is fixed permanently so it can not be lost.



SIMPLE TO USE

QUICK QUOTE

ONLINE PRICING

Push the grain sampler into the material in the closed position. Slowly open the sampler and because of the spiral design of the pockets, the bottom pocket will open first. Close the sampler, remove and empty through the handle.

Part No.	Length	No. of Sampling Points
675 1942A1000	985 mm	4
675 1942A1500	1485 mm	6
675 1942A2000	1985 mm	8
675 1942A2500	2485 mm	10