

Sack Master

The World's Best Range of High Quality Sack Samplers



The QAQC LAB Sack Master range has been specially designed to take samples through the side of a sack. A unique range of sample collection methods are available.

- Single point sampler
- Suitable for sampling free flowing powders and granules
- 316L stainless steel or HDPE

Operation:

1. Insert the sampler through the side of the sack.
2. Angle sampler downwards to allow the product to flow into the sample collecting container
3. Seal the hole using an Ultra Adhesive label (see pages 189-195).

A. Sack Sampler with Plain End

- Sample collecting bag is held over end of sampler
- Plain end



Part No.	Length	Diameter	End Fitting
675 1320A01	400mm	25mm	Plain



ONLINE PRICING ✓

B. Sack Sampler with End Cap

- Cap screws on to end of Sack Sampler
- Easily removed for cleaning
- Sample is retained in Sack Sampler



Part No.	Length	Diameter	End Fitting
675 1320B01	420mm	25mm	End Cap



ONLINE PRICING ✓

C. Sack Sampler with Bottle Adapter

- Adapter screws on to end of Sack Sampler
- Sample is collected in either a 250ml or 500ml bottle
- After sampling unscrew bottle and screw on the plastic bottle cap



Part No.	Length	Diameter	End Fitting
675 1320C01	420mm	25mm	Bottle Adapter*

* Sampler supplied with one 250ml Sample Bottle (Part no. 675 8165A250)

675 8165A250 250ml Bottle HDPE

675 8165A500 500ml Bottle HDPE

ONLINE PRICING ✓



Jumbo Sack Sampler

Wide diameter Sack Samplers

Our new range of Jumbo Sack Samplers have been introduced to meet the demand of sampling larger items such as nuts, grains and larger granules from sacks.

The Jumbo sack samplers are available in 2 lengths and 3 different styles:

- Suitable for sampling free flowing powders and granules
- Plain style - Simply hold over a bag
- End Cap - The sample is held in the sampler until the sample is deposited
- Bottle adapter - Sample drops straight into the bottle

C400 and C800 are supplied with a 1000ml sample bottle (spare bottle part no. 675 8126H1000).

Part No.	Length	Diameter	End Fitting	Material
675 1309A400	400mm	40mm	Plain	316L ss
675 1309B400	400mm	40mm	End Cap	316L ss
675 1309C400	400mm	40mm	Bottle Adapter	316L ss
675 1309A800	800mm	40mm	Plain	316L ss
675 1309B800	800mm	40mm	End Cap	316L ss
675 1309C800	800mm	40mm	Bottle Adapter	316L ss

ONLINE PRICING ✓



Disposable Sack Sampler

Pre-Sterilised Disposable Samplers

The disposable Sack Sampler is a hygienic, single use device that has been specially designed to take samples through the side of a sack.

- Suitable for sampling free flowing powders and granules
- Individually Bagged
- FDA & EU 10/2011 Conforming Materials
- BSE/TSE Free
- Full Batch Traceability
- Suitable for use in ATEX zones 0,1 and 2
- Available Sterile (gamma irradiated)

Operation:

1. Insert the sampler through the side of the sack.
2. Angle sampler downwards to allow the product to flow into the sample collecting bag
3. Seal the hole with an Ultra Adhesive label (see pages 189-195)



Part No.	Length	Diameter	Material	Sterile	Quantity per Box
675 8085A100	400mm	25mm	HDPE	No	100
675 8085A100S	400mm	25mm	HDPE	Yes	100
675 8085N100	400mm	14mm	HDPE	No	100
675 8085N100S	400mm	14mm	HDPE	Yes	100
675 8080A450	Sample Collecting Bag 450ml - for hygienic use - sterile		Qty: 1000 bags		
675 8080A900	Sample Collecting Bag 900ml - for hygienic use - sterile		Qty: 1000 bags		

ONLINE PRICING ✓